



GD104N

Mini-enclosure, gamma, 4 module, protect. class IP30, 1xPE, 1xN

Technical properties

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Number of modules	4
-------------------	---

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	40 A
---------------	------

Dimensions

Depth of installed product	82 mm
Height of installed product	180 mm
Width of installed product	110 mm
Width in division units	4

Cover, door

Type of door closing	non keylock
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Cover
Transparent cover or door	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	Yes
Neutral terminal block	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No