



GD104N

**Mini-enclosure, gamma, 4 module, protect. class IP30, 1xPE, 1xN**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

Protection main switch No

**Configuration**

Number of modules 4

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 40 A

**Dimensions**

Depth of installed product 82 mm

Height of installed product 180 mm

Width of installed product 110 mm

Width in division units 4

**Cover, door**

Type of door closing non keylock

Number of keylock of the door 0

Cover type With Notch

Door locking without

Cover type Cover

Transparent cover or door No

**Materials**

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	Yes
Neutral terminal block	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II