



GD106N

Mini-enclosure, gamma, 6 module, protect. class IP30, 1xPE, 1xN

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes
 Protection main switch No

Configuration

Number of modules 6

Compatibility

Suitable for Multimedia No

Electric current

Rated current 50 A

Dimensions

Depth of installed product 82 mm
 Internal depth 82 mm
 Height of installed product 180 mm
 Width of installed product 146 mm
 Width in division units 6

Cover, door

Type of door closing non keylock
 Number of keylock of the door 0
 Cover type With Notch
 Door locking without
 Cover type with notch
 Transparent cover or door No

Materials

Colour white
 Colour white
 RAL colour RAL 9010 - Pure white
 Material plastic

Installation, mounting

Suitable for outdoor use No

Settings

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II