



GD108E

Mini-enclosure, gamma, 8 module, protect. class IP30, 1xPE

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Number of modules	8
-------------------	---

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	82 mm
Internal depth	82 mm
Height of installed product	180 mm
Width of installed product	182 mm
Width in division units	8

Cover, door

Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	with notch
Transparent cover or door	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	Yes
Neutral terminal block	No
Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No