



GD108N

**Mini-enclosure, gamma, 8 module, protect. class IP30, 1xPE, 1xN**

### Technical properties

#### Functions

With a pipe-in lead	Yes
Protection main switch	No

#### Configuration

Number of modules	8
-------------------	---

#### Compatibility

Suitable for Multimedia	No
-------------------------	----

#### Main electrical features

Nominal voltage	230 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Depth of installed product	82 mm
Internal depth	82 mm
Height of installed product	180 mm
Width of installed product	182 mm
Width in division units	8

#### Cover, door

Type of door closing	non keylock
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	with notch
Transparent cover or door	No

#### Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

#### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

#### Settings

**Equipment**

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes

**Safety**

IK protection code against mechanical impacts	05
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No