



GD110N

Mini-enclosure, gamma, 10 module, protect. class IP30, 1xPE, 1xN

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes
 Protection main switch No

Configuration

Number of modules 10

Compatibility

Suitable for Multimedia No

Electric current

Rated current 63 A

Dimensions

Depth of installed product 82 mm
 Internal depth 82 mm
 Height of installed product 180 mm
 Width of installed product 218 mm
 Width in division units 10

Cover, door

Type of door closing non keylock
 Number of keylock of the door 0
 Cover type With Notch
 Door locking without
 Cover type with notch
 Transparent cover or door No

Materials

Colour white
 Colour white
 RAL colour RAL 9010 - Pure white
 Material plastic

Installation, mounting

Suitable for outdoor use No

Settings

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II