



GD113A



ENCLOSURE SURFACE GAMMA 13 M

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 13

Compatibility

Suitable for Multimedia No

Electric current

Rated current 63 A

Dimensions

Depth of installed product 103 mm

Height of installed product 250 mm

Width of installed product 250 mm

Width in division units 13

Cover, door

Type of door closing non keylock

Identification od protection index 40

Number of keylock of the door 0

Cover type optional

Materials

Copper weight of the product 0.015 kg

RAL colour RAL 9010 - Pure white

Material plastic

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 1

Quantity of section in width 1

Quantity of rails 1

Earthing terminal block Yes

Neutral terminal block Yes

Safety

Protection index IP

IP30

Protection class

isol.class I