



GD118A



Enclosure,gamma,surface mounting,18 Modules, version France

Technical properties

Architecture

Fixing mode surface-mounting

Configuration

Number of modules 18

Compatibility

Suitable for Multimedia No

Electric current

Rated current 63 A

Dimensions

Depth of installed product 103 mm

Internal depth 103 mm

Height of installed product 250 mm

Width of installed product 355 mm

Width in division units 18

Cover, door

Type of door closing non keylock

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type With Notch

Door locking without

Cover type Cover

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 1

Quantity of section in width 1

Quantity of rails 1

Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
---------------------	------