



GD213A



Enclosure,gamma,surface mounting,26 Modules, version France

Technical properties

Configuration

| | |
|-------------------|----|
| Number of modules | 26 |
|-------------------|----|

Compatibility

| | |
|-------------------------|----|
| Suitable for Multimedia | No |
|-------------------------|----|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 103 mm |
| Internal depth | 103 mm |
| Height of installed product | 375 mm |
| Width of installed product | 250 mm |
| Width in division units | 13 |

Cover, door

| | |
|------------------------------------|-------------|
| Type of door closing | non keylock |
| Identification od protection index | 40 |
| Interlockable | No |
| Number of keylock of the door | 0 |
| Cover type | With Notch |
| Door locking | without |
| Cover type | optional |
| Transparent cover or door | No |

Materials

| | |
|------------------------------|-----------------------|
| Copper weight of the product | 0.021 kg |
| Colour | RAL 9010 |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | plastic |

Settings

| | |
|----------------|---------------------------|
| Enclosure type | Distributor empty cabinet |
|----------------|---------------------------|

Equipment

| | |
|------------------------------|---|
| Number of rows | 2 |
| Quantity of section in width | 1 |
| Quantity of rails | 2 |

| | |
|-------------------------|-----|
| Can be accessorized | Yes |
| Earthing terminal block | Yes |
| Neutral terminal block | Yes |
| Signal passing door | Yes |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK05 |
|---|------|