



GD218A



Enclosure,gamma,surface mounting,36Modules, version France

Technical properties

Architecture

Fixing mode surface-mounting

Configuration

Number of modules 36

Compatibility

Suitable for Multimedia No

Electric current

Rated current 63 A

Dimensions

Depth of installed product 103 mm

Internal depth 103 mm

Height of installed product 375 mm

Width of installed product 355 mm

Width in division units 18

Cover, door

Type of door closing non keylock

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type With Notch

Door locking without

Cover type Cover

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 2

Quantity of section in width 1

Quantity of rails 2

Can be accessorized

Yes

Standards

European directive WEEE

not concerned

Safety

Protection index IP

IP30