



GD218A



**Enclosure,gamma,surface mounting,36Modules, version France**

**Technical properties**

**Configuration**

Number of modules	36
-------------------	----

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	103 mm
Internal depth	103 mm
Height of installed product	375 mm
Width of installed product	355 mm
Width in division units	18

**Cover, door**

Type of door closing	non keylock
Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Cover
Transparent cover or door	No

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	2
Quantity of section in width	1
Quantity of rails	2
Can be accessorized	Yes

**Standards**

Subject to technical modifications

**Safety**

---

IK protection code against mechanical impacts	IK05
REACH conform	No
RoHS conform	Yes
Halogen free	No