



GD313A



## ENCLOSURE SURFACE GAMMA 39 M

### Technical properties

#### Architecture

Fixing mode surface-mounting

#### Functions

With a pipe-in lead Yes

#### Configuration

Number of modules 39

#### Compatibility

Suitable for Multimedia No

#### Electric current

Rated current 63 A

#### Dimensions

Depth of installed product 103 mm

Height of installed product 500 mm

Width of installed product 250 mm

Width in division units 13

#### Cover, door

Type of door closing non keylock

Identification od protection index 40

Number of keylock of the door 0

Cover type optional

#### Materials

Copper weight of the product 0.041 kg

RAL colour RAL 9010 - Pure white

#### Settings

Enclosure type Distributor empty cabinet

#### Equipment

Number of rows 3

Quantity of section in width 1

Quantity of rails 3

Earthing terminal block Yes

Neutral terminal block Yes

Signal passing door Yes

**Safety**

---

IK protection code against mechanical impacts

IK05

---

Protection class

isol.class I