



GD318A



Enclosure,gamma,surface mounting,54 Modules, version France

Technical properties

Configuration

Number of modules	54
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	103 mm
Internal depth	103 mm
Height of installed product	500 mm
Width of installed product	355 mm
Width in division units	18

Cover, door

Type of door closing	non keylock
Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Cover
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Earthing terminal block	Yes

Neutral terminal block	Yes
Safety	
IK protection code against mechanical impacts	IK05
REACH conform	No
RoHS conform	Yes
Halogen free	No