



GD413A



## ENCLOSURE SURFACE GAMMA 52 M

### Technical properties

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Functions

With a pipe-in lead	Yes
---------------------	-----

#### Configuration

Number of modules	52
-------------------	----

#### Compatibility

Suitable for Multimedia	No
-------------------------	----

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Depth of installed product	103 mm
Height of installed product	625 mm
Width of installed product	250 mm
Width in division units	13

#### Cover, door

Identification od protection index	40
Number of keylock of the door	0

#### Materials

Copper weight of the product	0.048 kg
RAL colour	RAL 9010 - Pure white
Material	plastic

#### Equipment

Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

#### Safety

IK protection code against mechanical impacts	IK05
---	------

Protection index IP	IP30
Protection class	isol.class I