



HA7100080

## Slotted panel trunking halogenfree HA7 100x80mm light grey

### Technical properties

#### Architecture

Flexible No

#### Configuration

Side wall configuration Slotted

#### Electric current

Current leak stable Yes

#### Dimensions

Trunking height 100 mm

Length 2000 mm

Trunking width 80 mm

Slot width 6 mm

Tongue width 6.5 mm

#### Cover, door

Lid shape loose

#### Materials

RAL colour RAL 7035 - Light grey

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

#### Cable

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 272

Internal/useful cross section 6738 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 195

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 378

#### Standards

Approvals EN50085-2-3

European directive RoHS voluntary compliance

UL 94 classification V0

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Fireproof classification	M1

**temperatur**

---

Ambient temperature	-25...90 °C
---------------------	-------------