



HA7100100

Slotted panel trunking halogenfree HA7 100x100mm light grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 100 mm

Length 2000 mm

Trunking width 100 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 346

Internal/useful cross section 8488 mm²

Number of wires 2,5 mm² - 40% filling degree 247

Number of wires 1,0 mm² - 40% filling degree 480

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

Fireproof classification

M1

temperatur

Ambient temperature

-25...90 °C