



HA740025

**slotted panel trunking HA7 40x25, light grey**

**Technical properties**

**Architecture**

Flexible No

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 40 mm

Length 2000 mm

Trunking width 25 mm

Slot width 6 mm

Tongue width 6.5 mm

**Cover, door**

Lid shape loose

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Material PC-ABS

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching EN 50085-2-3:1999

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 22

Internal/useful cross section 605 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 15

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 30

**Standards**

European directive RoHS voluntary compliance

UL 94 classification V0

**Safety**

---

Fireproof classification

M1

**temperatur**

---

Ambient temperature

-25...90 °C