



HA760120

slotted panel trunking HA7 60x120, light grey

Technical properties

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	120 mm
Slot width	6 mm
Tongue width	6.5 mm

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	EN 50085-2-3:1999
---------------	-------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	211
Internal/useful cross section	5558 mm ²
Number of wires 2,5 mm ² - 40% filling degree	151
Number of wires 1,0 mm ² - 40% filling degree	294

Standards

European directive RoHs	voluntary compliance
UL 94 classification	V0

Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Fireproof classification	M1
temperatur	
Ambient temperature	-25...90 °C