



HA780025

Slotted panel trunking halogenfree HA7 80x25mm light grey

Technical properties

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	80 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	25 mm
----------------	-------

Slot width	6 mm
------------	------

Tongue width	6.5 mm
--------------	--------

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Material	PC-ABS
----------	--------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	EN 50085-2-3:1999
---------------	-------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	56
--	----

Internal/useful cross section	1485 mm ²
-------------------------------	----------------------

Number of wires 2,5 mm ² - 40% filling degree	40
--	----

Number of wires 1,0 mm ² - 40% filling degree	78
--	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

UL 94 classification	V0
----------------------	----

Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Fireproof classification	M1
temperatur	
Ambient temperature	-25...90 °C