



HIC402A

Motorized changeover switch 4P 20A 400V

Technical properties

Architecture

Number of poles	4 P
Type of pole	4 P

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	20 A
Rated short-time withstand current 1s	4 kA

Power

Total power loss under I _N	0.6 W
Power loss per pole at I _N	0.2 W

Standards

European directive WEEE	not concerned
-------------------------	---------------