



HIC402A

**Motorized changeover switch 4P 20A 400V**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	4 P

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Electric current**

Rated current	20 A
Rated short-time withstand current 1s	4 kA

**Power**

Total power loss under I <sub>N</sub>	0.6 W
Power loss per pole at I <sub>N</sub>	0.2 W

**Standards**

European directive WEEE	not concerned
-------------------------	---------------