



HIC406A

**Motorized changeover switch 4P 63A 400V**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

**Functions**

Reversing switch	Yes
------------------	-----

**Controls and indicators**

Motor drive integrated	Yes
------------------------	-----

**Main electrical features**

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

**Electric current**

Rated current	63 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	4 kA
Rated operational current in AC23 category A	63 A

**Power**

Total power loss under I <sub>N</sub>	3.6 W
Power loss per pole at I <sub>N</sub>	1.2 W
Contact rating with 400 V in AC1	41 kW

**Cover, door**

Interlockable	Yes
---------------	-----

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

**Standards**

Standard text	IEC 60947-3 ; IEC 60947-6
European directive WEEE	concerned

