



HNG2502507035B

Slotted panel trunking made of PPO halogenfree HNG 25x25mm light grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 25 mm

Length 2000 mm

Trunking width 25 mm

Slot width 5 mm

Tongue width 7.5 mm

Cover, door

Lid shape loose

Materials

RAL colour RAL 7035 - Light grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 19

Internal/useful cross section 413 mm²

Number of wires 2,5 mm² - 40% filling degree 14

Number of wires 1,0 mm² - 40% filling degree 27

Standards

European directive RoHS voluntary compliance

UL 94 classification V1

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
temperatur	
Ambient temperature	-25...90 °C