



HNG3705007035B

Slotted panel trunking PPO halogenfree HNG 37x50mm light grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 37 mm

Length 2000 mm

Trunking width 50 mm

Slot width 5 mm

Tongue width 7.5 mm

Cover, door

Lid shape loose

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Material PPO

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 65

Internal/useful cross section 1400 mm²

Number of wires 2,5 mm² - 40% filling degree 47

Number of wires 1,0 mm² - 40% filling degree 91

Standards

European directive RoHs voluntary compliance

UL 94 classification V1

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

temperatur

Ambient temperature	-25...90 °C
---------------------	-------------