



HNG5005007035B

**Slotted panel trunking cover PPO HNG 50x50mm light grey**

**Technical properties**

**Architecture**

Flexible No

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 50 mm

Length 2000 mm

Trunking width 50 mm

Slot width 5 mm

Tongue width 7.5 mm

**Cover, door**

Lid shape loose

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Material PPO

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching EN 50085-2-3:1999

Fixing type bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 92

Internal/useful cross section 1974 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 66

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 128

**Standards**

European directive RoHs voluntary compliance

UL 94 classification V1

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**temperatur**

---

Ambient temperature	-25...90 °C
---------------------	-------------