



HNG5007507035B

Slotted panel trunking PPO halogenfree HNG 50x75mm light grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 50 mm

Length 2000 mm

Trunking width 75 mm

Slot width 5 mm

Tongue width 7.5 mm

Cover, door

Lid shape loose

Materials

RAL colour RAL 7035 - Light grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 142

Internal/useful cross section 3031 mm²

Number of wires 2,5 mm² - 40% filling degree 101

Number of wires 1,0 mm² - 40% filling degree 197

Standards

European directive RoHS voluntary compliance

UL 94 classification V1

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
temperatur	
Ambient temperature	-25...90 °C