



HTG411H

## Multi energy data logger & server + micro SD card

### Technical properties

#### Architecture

Fixing mode DIN rail type O (symmetrical)

#### Configuration

Number of modules 6

#### Controls and indicators

With LED indication Yes

#### Connectivity

Protocol TCP/IP

Other bus systems other

Model System interface/media gateway for bus system Ethernet interface

#### Voltage

Operating voltage 24 V

#### Equipment

Number of digital inputs 2

Number of USB interfaces 2

Demounting protection No

Bidirectional radio frequency No

Radio interface No

IR interface No

Updateable Yes

Visualization No

Web-Server Yes

Number of analogical inputs 2

#### Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -25...70 °C

Storage/transport temperature -55...85 °C