



HTG411H

Multi energy data logger & server + micro SD card

Technical properties

Configuration

Number of modules	6
-------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Connectivity

Protocol	TCP/IP
----------	--------

Other bus systems	other
-------------------	-------

Model System interface/media gateway for bus system	Ethernet interface
---	--------------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

Operating voltage	24 V
-------------------	------

Power

Power consumption	7 VA
-------------------	------

Equipment

Number of digital inputs	2
--------------------------	---

Number of USB interfaces	2
--------------------------	---

Demounting protection	No
-----------------------	----

Bidirectional radio frequency	No
-------------------------------	----

Radio interface	No
-----------------	----

IR interface	No
--------------	----

Updateable	Yes
------------	-----

Visualization	No
---------------	----

Web-Server	Yes
------------	-----

Number of analogical inputs	2
-----------------------------	---

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	No
---------------	----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-55...85 °C
