



HXA021H

**Auxiliary contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Main electrical features**

Rated operational voltage Ue	230 V
------------------------------	-------

**Voltage**

Rated operational voltage in DC	125 V
---------------------------------	-------

**Power**

Total power loss under IN	3 W
---------------------------	-----

**Connection**

Type of contacts	1 NO/NC
Type of connection	quick connect

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP4X
---------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m