



HXA021H

**Auxiliary contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Main electrical features**

Rated operational voltage Ue 230 V

**Voltage**

Rated operational voltage in DC 125 V

**Power**

Total power loss under IN 3 W

**Connection**

Type of contacts 1 NO/NC

Type of connection quick connect

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m