



HXA025H

Auxiliary low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)

Technical properties

Architecture

Fixing mode Clipped

Main electrical features

Rated operational voltage Ue 125 V

Voltage

Rated operational voltage in DC 30 V

Power

Total power loss under IN 3 W

Connection

Type of contacts 1 NO/NC

Type of connection quick connect

Use conditions

Degree of pollution according to IEC 60664 /
IEC 60947-2 3

Altitude 2000 m