



HXA025H

**Auxiliary low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Main electrical features**

Rated operational voltage Ue 125 V

**Voltage**

Rated operational voltage in DC 30 V

**Power**

Total power loss under IN 3 W

**Connection**

Type of contacts 1 NO/NC

Type of connection quick connect

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP4X

**Use conditions**

Degree of pollution according to IEC 60664 /  
IEC 60947-2 3

Altitude 2000 m