



HXA025H

**Auxiliary low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)**

#### Technical properties

##### Architecture

Fixing mode	Clipped
-------------	---------

##### Main electrical features

Rated operational voltage Ue	125 V
------------------------------	-------

##### Voltage

Rated operational voltage in DC	30 V
---------------------------------	------

##### Power

Total power loss under IN	3 W
---------------------------	-----

##### Connection

Type of contacts	1 NO/NC
------------------	---------

Type of connection	quick connect
--------------------	---------------

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
---	---

Altitude	2000 m
----------	--------