



HXA055H

UVR delayed 380-450V AC (x160-P160-x250-P250)

Technical properties

Voltage

DC control voltage	0 V
Command voltage AC	380 / 450 V

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	2.3 W
---------------------------	-------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m