



HXB040H

Motor operator x250 24V DC

Technical properties

Architecture

| | |
|---------------|-------------|
| Type of order | motor drive |
|---------------|-------------|

Main electrical features

| | |
|------------------------------|-----|
| Rated operational voltage Ue | 0 V |
| Type of supply voltage | DC |

Voltage

| | |
|---------------------------------|------|
| DC control voltage | 24 V |
| Command voltage AC | 0 V |
| Rated operational voltage in DC | 24 V |

Frequency

| | |
|-----------|------|
| Frequency | 0 Hz |
|-----------|------|

Power

| | |
|---------------------------|------|
| Total power loss under IN | 24 W |
|---------------------------|------|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

Use conditions

| | |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |