



HXB042H

Motor operator x250 230-240VAC

Technical properties

Main electrical features

Rated operational voltage Ue	220 / 240 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

DC control voltage	0 V
Command voltage AC	230 / 240 V
Rated operational voltage in DC	0 V

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	24 W
---------------------------	------

Standards

European directive RoHs	voluntary compliance
European directive WEEE	concerned

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m