



HXC021H

Auxiliary contact 1NO+1NC 230V AC (h250-h400-h630-h800-h1000-h1600)

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated operational voltage Ue 230 V

Voltage

Rated operational voltage in DC 125 V

Power

Total power loss under IN 3 W

Connection

Type of contacts 1 NO/NC

Type of connection with screw

Standards

European directive WEEE concerned

Safety

Protection index IP IP4X

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m