



HXC025H

Auxilirary low level 1NO+1NC 125V AC (h250-h400-h630-h800-h1000-h1600)

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated operational voltage Ue	125 V
------------------------------	-------

Voltage

Rated operational voltage in DC	30 V
---------------------------------	------

Power

Total power loss under IN	3 W
---------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m