



HXC026H

Alarm contact low level 1NO+1NC (h250-h400-h630-h800-h1000-h1600)

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated operational voltage U_e 125 V

Voltage

Rated operational voltage in DC 30 V

Power

Total power loss under IN 3 W

Standards

European directive WEEE concerned

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m