



HXC051H

## Undervoltage release with delay h250-h630 24V DC

### Technical properties

#### Voltage

|                    |      |
|--------------------|------|
| DC control voltage | 24 V |
| Command voltage AC | 0 V  |

#### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0.5 W |
|---------------------------|-------|

#### Equipment

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |
| Number of auxiliary contacts as change-over contact     | 0 |

#### Use conditions

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |