



HXC055H

Undervoltage release with delay h250-h630 380-415V AC

Technical properties

Voltage

| | |
|--------------------|-------------|
| DC control voltage | 0 V |
| Command voltage AC | 380 / 415 V |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 1.5 W |
|---------------------------|-------|

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |

Use conditions

| | |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |