



HXE054H

## Undervoltage Release delayed h800-h1000 3P 220-240VAC

### Technical properties

#### Voltage

|                    |             |
|--------------------|-------------|
| DC control voltage | 0 V         |
| Command voltage AC | 220 / 240 V |

#### Frequency

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

#### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 2.9 W |
|---------------------------|-------|

#### Equipment

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |
| Number of auxiliary contacts as change-over contact     | 0 |

#### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

#### Use conditions

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |