



HXF001H

### Shunt trip Release h1600 24V DC

#### Technical properties

##### Voltage

|                    |      |
|--------------------|------|
| DC control voltage | 24 V |
| Command voltage AC | 0 V  |

##### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0.7 W |
|---------------------------|-------|

##### Equipment

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |
| Number of auxiliary contacts as change-over contact     | 0 |

##### Use conditions

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |