



HXF040H

Motor operator h1250-h1600 24V DC

Technical properties

Main electrical features

Rated operational voltage Ue	0 V
------------------------------	-----

Voltage

DC control voltage	24 V
Command voltage AC	0 V
Rated operational voltage in DC	24 V

Frequency

Frequency	0 Hz
-----------	------

Power

Total power loss under IN	24 W
---------------------------	------

Standards

European directive RoHs	voluntary compliance
European directive WEEE	concerned

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m