



HXF040H

**Motor operator h1250-h1600 24V DC**

**Technical properties**

**Architecture**

Type of order motor drive

**Main electrical features**

Rated operational voltage Ue 0 V

Type of supply voltage DC

**Voltage**

DC control voltage 24 V

Command voltage AC 0 V

Rated operational voltage in DC 24 V

**Frequency**

Frequency 0 Hz

**Power**

Total power loss under IN 24 W

**Standards**

European directive RoHS voluntary compliance

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m