



HXF055H

## Undervoltage Release delayed h800-h1600 4P 380-415VAC

### Technical properties

#### Voltage

DC control voltage	0 V
Command voltage AC	380 / 415 V

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	2.1 W
---------------------------	-------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m