



HXT040H

Motor Operator P250 24VDC with Auto-Reset

Technical properties

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

DC control voltage	24 V
--------------------	------

Command voltage AC	0 V
--------------------	-----

Electric current

Inrush current OFF-RESET	24V DC - 27A
--------------------------	--------------

Inrush current ON	24V DC - 14.1A
-------------------	----------------

Operating current OFF-RESET	24V DC - 14.1A
-----------------------------	----------------

Operating current ON	24V DC - 14.1A
----------------------	----------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Altitude	2000 m
----------	--------