



HXT040H

**Motor Operator P250 24VDC with Auto-Reset**

**Technical properties**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage DC

**Voltage**

DC control voltage 24 V

Command voltage AC 0 V

**Electric current**

Inrush current OFF-RESET 24V DC - 27A

Inrush current ON 24V DC - 14.1A

Operating current OFF-RESET 24V DC - 14.1A

Operating current ON 24V DC - 14.1A

**Standards**

European directive RoHS voluntary compliance

European directive WEEE concerned

**Use conditions**

Altitude 2000 m