



HXT040HK

Motor Operator P250 24VDC with Auto-Reset + key

Technical properties

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage DC

Voltage

DC control voltage 24 V

Command voltage AC 0 V

Electric current

Inrush current OFF-RESET 24V DC - 27A

Inrush current ON 24V DC - 14.1A

Operating current OFF-RESET 24V DC - 14.1A

Operating current ON 24V DC - 14.1A

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m