



HXT042HK

**Motor Operator P250 230-240VAC with Auto-Reset + key**

**Technical properties**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage AC

**Voltage**

DC control voltage 0 V

Command voltage AC 230 / 240 V

**Electric current**

Inrush current OFF-RESET 230-240V AC - 6A

Inrush current ON 230-240V AC - 6A

Operating current OFF-RESET 230-240V AC - 3.4A

Operating current ON 230-240V AC - 3.4A

**Frequency**

Frequency 50 to 60 Hz

**Standards**

European directive RoHS compliant

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m